

Çan vantuz (oval)

SAOG-S 80x30 NBR-60 M10-AG




Art.-Nr.: 10.01.01.12303



SAOG-S 80x30 NBR-60 M10-AG

Teknik veriler

Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	60,0 Shore A
Bağlantı	M10-AG
Boyutlar (LxW)	80x30
Meme ucu malzemesi	Çelik



Tasarım verileri SAOG-S 80x30 NBR-60 M10-AG

Tasarım verileri

Yükseklik H	33,50 mm
Nominal çap dn	4,00 mm
Diş G1	M10-M
Diş uzunluğu LG1	10,0 mm
Anahtar boyutu SW1	16,0 mm
Yay stroku Z	6,0 mm
Vantuz genişliği Bs	30,90 mm
Ls	80,90 mm
Lmaks.(S)	86,50 mm
Bmax(S)	37,50 mm



WWW.SCHMALZ.COM/10.01.01.12303

Art.-Nr.: 10.01.01.12303

**Teknik veriler**

Vantuz malzemesi	Nitril kauçuk NBR
Hortum çapı (tavsiye edilen) d	4,0 mm
İş parçası yarıçapı dak (dışbükey)	20,0 mm
Emme kuvveti (-600mbar)	105,00 N
Ağırlık	34,10 g
Boyutlar (LxW)	80 x 30
Yanal kuvvet	130,0 N
Yanal kuvvet yağlı yüzey	91,0 N
Cilt	11,000 cm ³
Körük Sayısı	0,0
Ürün ailesi	SAOG-S

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

