

Çan vantuz (oval)

SAOG-S 95x40 NBR-60 M10-AG




Art.-Nr.: 10.01.01.12304



SAOG-S 95x40 NBR-60 M10-AG

Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	60,0 Shore A
Bağlantı	M10-AG
Boyutlar (LxW)	95x40
Meme ucu malzemesi	Çelik



Tasarım verileri

Attribute	Value
Yükseklik H	33,50 mm
Nominal çap dn	4,00 mm
Diş G1	M10-M
Diş uzunluğu LG1	10,0 mm
Anahtar boyutu SW1	16,0 mm
Yay stroku Z	6,0 mm
Vantuz genişliği Bs	40,60 mm
Ls	95,60 mm
Lmaks.(S)	101,00 mm
Bmax(S)	46,00 mm

Tasarım verileri SAOG-S 95x40 NBR-60 M10-AG



WWW.SCHMALZ.COM/10.01.01.12304

Art.-Nr.: 10.01.01.12304

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Hortum çapı (tavsiye edilen) d	6,0 mm
İş parçası yarıçapı dak (dışbükey)	35,0 mm
Emme kuvveti (-600mbar)	165,00 N
Ağırlık	49,70 g
Boyutlar (LxW)	95 x 40
Yanal kuvvet	192,0 N
Yanal kuvvet yağlı yüzey	110,0 N
Cilt	18,000 cm ³
Körük Sayısı	0,0
Ürün ailesi	SAOG-S

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12304

WWW.SCHMALZ.COM/10.01.01.12304