



Art.-Nr.: 10.01.01.12350



SAF 30 HT2-65 G3/8-IG

Присоска SAF HT2, доступная в различных диаметрах, доставляется с соединительным ниппелем, вулканизированным в эластомерную часть.



Конструктивные данные SAF 30 HT2-65 G3/8-IG

Технические данные

Attribute	Value
Материал присоски	Высокотемпературный материал HT2
Твердость материала [Shore A]	65,0 Shore A
размер	30,00
Термостойкость	200,0 °C
Соединение	G3/8-IG
Материал ниппеля	никелированный

Конструктивные данные

Attribute	Value
Высота H	36,00 mm
Номинальный диаметр dn	4,00 mm
Резьба G1	G3/8"-F
Длина резьбы LG1	9,0 mm
Размер гаечного ключа SW1	22,0 mm
Ход пружины Z	3,0 mm
Диаметр Ds	31,0 mm
Диаметр Dmax(S)	34,0 mm

Плоская присоска (круглая)

SAF 30 HT2-65 G3/8-IG



Art.-Nr.: 10.01.01.12350



Технические данные

Attribute	Value
Всасывающая сила (-600 мбар)	38,00 N
размер	30,00
Термостойкость	200,0 °C
Количество складок	0,0
Семейство продуктов	SAF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12350



Данные для заказа Аксессуары 10.01.01.12350

Тип		Количество предметов
Чехол присоски	SU 30	10.01.01.12889



WWW.SCHMALZ.COM/10.01.01.12350