


Düz vantuz (yuvarlak)

SAF 30 HT2-65 G3/8-IG



Art.-Nr.: 10.01.01.12350




Teknik veriler

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT2
Malzeme sertliği [Shore A]	65,0 Shore A
Boyut	30,00
Sıcaklık direnci	200,0 °C
Bağlantı	G3/8-IG
Meme ucu malzemesi	Nikel kaplama

SAF 30 HT2-65 G3/8-IG

Çeşitli çaplarda mevcut olan vantuz SAF HT2, elastomer parçaya vulkanize edilmiş bağlantı nipeli ile birlikte teslim edilir.



Tasarım verileri

Attribute	Value
Yükseklik H	36,00 mm
Nominal çap dn	4,00 mm
Diş G1	G3/8"-F
Diş uzunluğu LG1	9,0 mm
Anahtar boyutu SW1	22,0 mm
Yay stroku Z	3,0 mm
Çap Ds	31,0 mm
Çap Dmax(S)	34,0 mm

Tasarım verileri SAF 30 HT2-65 G3/8-IG



WWW.SCHMALZ.COM/10.01.01.12350

Düz vantuz (yuvarlak)

SAF 30 HT2-65 G3/8-IG



Art.-Nr.: 10.01.01.12350



Teknik veriler

Attribute	Value
Emme kuvveti (-600mbar)	38,00 N
Boyut	30,00
Sıcaklık direnci	200,0 °C
Körük Sayısı	0,0
Ürün ailesi	SAF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12350



Sipariş Verisi Aksesuarlar 10.01.01.12350

Typ	Ürün numarası
Vantuz kapağı	SU 30
	10.01.01.12889



WWW.SCHMALZ.COM/10.01.01.12350