

Düz vantuz (yuvarlak)

SAF 50 HT2-65 G1/4-IG



Art.-Nr.: 10.01.01.12356




Teknik veriler

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT2
Malzeme sertliği [Shore A]	65,0 Shore A
Boyut	50,00
Sıcaklık direnci	200,0 °C
Bağlantı	G1/4-IG
Meme ucu malzemesi	Nikel kaplama

SAF 50 HT2-65 G1/4-IG

Çeşitli çaplarda mevcut olan vantuz SAF HT2, elastomer parçaya vulkanize edilmiş bağlantı nipeli ile birlikte teslim edilir.



Tasarım verileri

Attribute	Value
Yükseklik H	33,00 mm
Nominal çap dn	6,00 mm
Diş G1	G1/4"-F
Diş uzunluğu LG1	15,0 mm
Anahtar boyutu SW1	22,0 mm
Yay stroku Z	5,0 mm
Çap Ds	50,0 mm
Çap Dmax(S)	56,0 mm

Tasarım verileri SAF 50 HT2-65 G1/4-IG



WWW.SCHMALZ.COM/10.01.01.12356

Düz vantuz (yuvarlak)

SAF 50 HT2-65 G1/4-IG



Art.-Nr.: 10.01.01.12356



Teknik veriler

Attribute	Value
Emme kuvveti (-600mbar)	100,00 N
Boyut	50,00
Sıcaklık direnci	200,0 °C
Körük Sayısı	0,0
Ürün ailesi	SAF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12356



Sipariş Verisi Aksesuarlar 10.01.01.12356

Typ	Ürün numarası
Vantuz kapağı	SU 50
	10.01.01.12837



WWW.SCHMALZ.COM/10.01.01.12356