

Flat suction cup (round)

SAF 60 HT2-65 G1/4-IG



Art.-Nr.: 10.01.01.12360



SAF 60 HT2-65 G1/4-IG


Suction cup SAF HT2, available in various diameters, is delivered with connection nipple vulcanized to elastomer part.

Technical data

Attribute	Value
Suction cup material	High temperature material HT2
Material hardness [Shore A]	65.0 Shore A
Size	60.00
Temperature resistance	200.0 °C
Connection	G1/4-IG
Nipple material	Nickel plated

Design data

Attribute	Value
Height H	36.00 mm
Nominal diameter dn	6.00 mm
Thread G1	G1/4"-F
Thread length LG1	15.0 mm
Key width SW1	22.0 mm
Spring stroke Z	6.0 mm
Diameter Ds	60.6 mm
Diameter Dmax(S)	67.0 mm



Design data SAF 60 HT2-65 G1/4-IG



WWW.SCHMALZ.COM/10.01.01.12360

Flat suction cup (round)

SAF 60 HT2-65 G1/4-IG



Art.-Nr.: 10.01.01.12360



Technical data

Attribute	Value
Suction force (-600mbar)	150.00 N
Size	60.00
Temperature resistance	200.0 °C
Number of folds	0.0
Product family	SAF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12360



Ordering Data Accessories 10.01.01.12360

Typ		Item number
Suction cup cover	SU 60	10.01.01.13585



WWW.SCHMALZ.COM/10.01.01.12360