

Flat suction cup (round)

SGPN 30 HT1-60 G1/4-AG



Art.-Nr.: 10.01.01.12399



Technical data


Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Size	30.00
Vacuum connection	G 1/4"-M
Nipple material	Aluminum

SGPN 30 HT1-60 G1/4-AG

Flat suction cup SGPN (elastomer part + connection nipple) is delivered unassembled. The delivery consists of:

- Suction cup of type SGP – elastomer part, available in various diameters and materials
- Connection nipple of type SA-NIP – available with various threads

Available spare parts: suction cup SGP, connection nipple SA-NIP



Design data

Height H	27.20 mm
Nominal diameter dn	5.50 mm
Thread G1	G 1/4"-M
Thread length LG1	10.0 mm
Key width SW1	17.0 mm
Spring stroke Z	2.0 mm
Diameter Ds	30.0 mm
Diameter Dmax(S)	32.0 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data SGPN 30 HT1-60 G1/4-AG



WWW.SCHMALZ.COM/10.01.01.12399

1

Flat suction cup (round)

SGPN 30 HT1-60 G1/4-AG



Art.-Nr.: 10.01.01.12399



Technical data

Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Suction force (-600mbar)	19.00 N
Weight	12.10 g
Volume	3.000 cm ³
Size	30.00
Number of folds	0.0
Product family	SGPN

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Ordering Data Spare Parts 10.01.01.12399

Typ	Item number
Suction Cup Connection Nipples	SA-NIP N033 G1/4-AG DN550 10.01.01.00818



Ordering Data Wear Parts 10.01.01.12399

Typ	Item number
Flat suction cup (round)	SGP 30 HT1-60 N033 10.01.01.12395



WWW.SCHMALZ.COM/10.01.01.12399