




SAOK 70x25 NBR-60 G3/8-IG

Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	60,0 Shore A
Boyutlar (LxW)	70 x 25
Bağlantı	G3/8-IG
Meme ucu malzemesi	Pirinç



Tasarım verileri SAOK 70x25 NBR-60 G3/8-IG

Tasarım verileri

Attribute	Value
Yükseklik H	35,50 mm
Nominal çap dn	6,00 mm
Diş G1	G3/8"-F
Diş uzunluğu LG1	9,0 mm
Anahtar boyutu SW1	22,0 mm
Yay stroku Z	12,8 mm
Vantuz genişliği Bs	22,60 mm
Ls	67,20 mm
Lmaks.(S)	71,00 mm

Art.-Nr.: 10.01.01.12460



Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Hortum çapı (tavsiye edilen) d	6,0 mm
Çekme kuvveti	81,00 N
Ağırlık	47,80 g
Boyutlar (LxW)	70 x 25
Yanal kuvvet	46,0 N
Yanal kuvvet yağlı yüzey	20,0 N
Körük Sayısı	0,0
Çekme kuvveti yağlı yüzey	60,00 N
İş parçası açısı W dak	80,0 °
Ürün ailesi	SAOK

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12460



WWW.SCHMALZ.COM/10.01.01.12460