

Edge gripper suction cup (oval)

SAOK 70x25 HT2-65 G3/8-IG




Art.-Nr.: 10.01.01.12463



SAOK 70x25 HT2-65 G3/8-IG

Technical data

Attribute	Value
Suction cup material	High temperature material HT2
Material hardness [Shore A]	65.0 Shore A
Dimension (LxW)	70 x 25
Connection	G3/8-IG
Nipple material	Brass



Design data SAOK 70x25 HT2-65 G3/8-IG

Design data

Attribute	Value
Height H	35.50 mm
Nominal diameter dn	6.00 mm
Thread G1	G3/8"-F
Thread length LG1	9.0 mm
Key width SW1	22.0 mm
Spring stroke Z	12.8 mm
Suction cup width Bs	22.60 mm
Ls	67.20 mm
Lmax.(S)	71.00 mm



WWW.SCHMALZ.COM/10.01.01.12463

Art.-Nr.: 10.01.01.12463

**Technical data**

Attribute	Value
Suction cup material	High temperature material HT2
Hose inner diameter (recom.) d	6.0 mm
Pull-off force	75.00 N
Weight	53.9 g
Dimension (LxW)	70 x 25
Lateral force	42.0 N
Number of folds	0.0
Pull-off force oily surface	59.00 N
Workpiece angle W min.	80.0 °
Product family	SAOK

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12463

