

**Teknik veriler**


Attribute	Value
Malzeme	Alüminyum
Şekil	Standart Akış
Basınçlı hava bağlantısı	G1/8"-F
Çap	40,0 mm

SBS 40 SF G1/8-IG AL

Floating vantuz SBS monte edilmiş olarak teslim edilir. Montaj şunlardan oluşur:

- SBS tipi floating vantuz - çeşitli çaplarda mevcuttur
- HT1 malzemesinden yapılmış elastomer tampon
- İsteğe bağlı ürün ilavesi: merkezi destek

Mevcut yedek parçalar: Elastomer tampon, sürtünme halkası

**Tasarım verileri SBS 40 SF G1/8-IG AL****Tasarım verileri**

Attribute	Value
Genişlik B	41,00 mm
Yükseklik H1	17,40 mm
Yükseklik H	17,00 mm
Dış çap D	40,00 mm
Dış G1	G1/8"-F
Dış uzunluğu LG1	5,0 mm
Dış G2	M4-F
Dış uzunluğu LG2	6,0 mm
Dış uzunluğu LG3	6,0 mm
Delik aralığı X1	32,0 mm
Dış G3	G1/8"-F

Art.-Nr.: 10.01.01.12638

**Teknik veriler**

Attribute	Value
Ağırlık	51,00 g
Hava tüketimi [l/dak]	100,0 l/min
Hava tüketimi	6,000 m³/h
Tutma kuvveti	6,5 N
Basınç aralığı (çalışma basıncı) [bar]	1,0 ... 6,0 bar
Ürün ailesi	SBS

Note: Air consumption: The values provided are based on an operating pressure of 5 bar, measured on a suction-tight workpiece. The actual values may differ depending on the properties of the workpiece.

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12638

**Sipariş Verisi Yedek Parça 10.01.01.12638**

Typ	Ürün numarası
Sürtünme yüzeyi (f. spec. tutucular) REIB-FL SBS HT1-60	10.01.01.12593

