

Düz vantuz (yuvarlak)

SGP 40 SI-50 N035




Art.-Nr.: 10.01.01.12772



SGP 40 SI-50 N035

Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	50.0 Shore A
Boyut	40.00



Tasarım verileri SGP 40 SI-50 N035

Tasarım verileri

Attribute	Value
Yükseklik H2	14.50 mm
Yükseklik H	20.60 mm
Kafa çapı Dk	16.0 mm
İç çap d	8.00 mm
Yay stroku Z	2.3 mm
Çap Ds	40.0 mm
Çap Dmax(S)	42.0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



WWW.SCHMALZ.COM/10.01.01.12772

Düz vantuz (yuvarlak)

SGP 40 SI-50 N035



Art.-Nr.: 10.01.01.12772



Teknik veriler

Attribute	Value
Meme ucu ailesi	N 035
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	50.0 Shore A
Emme kuvveti (-600mbar)	33.00 N
Ağırlık	5.2 g
Cilt	3.800 cm ³
Boyut	40.00
Körük Sayısı	0.0
Ürün ailesi	SGP

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12772



WWW.SCHMALZ.COM/10.01.01.12772