


Düz vantuz (yuvarlak)

SGP 35 SI-50 N034




Art.-Nr.: 10.01.01.12784



SGP 35 SI-50 N034

Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	50,0 Shore A
Boyut	35,00



Tasarım verileri SGP 35 SI-50 N034

Tasarım verileri

Attribute	Value
Yükseklik H2	14,80 mm
Yükseklik H	23,50 mm
Kafa çapı Dk	16,5 mm
İç çap d	10,00 mm
Yay stroku Z	0,5 mm
Çap Ds	30,2 mm
Çap Dmax(S)	35,0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



WWW.SCHMALZ.COM/10.01.01.12784

Düz vantuz (yuvarlak)

SGP 35 SI-50 N034



Art.-Nr.: 10.01.01.12784



Teknik veriler

Attribute	Value
Meme ucu ailesi	N 034
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	50,0 Shore A
Emme kuvveti (-600mbar)	31,00 N
Ağırlık	6,4 g
Cilt	2,800 cm ³
Boyut	35,00
Körük Sayısı	0,0
Ürün ailesi	SGP

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12784



WWW.SCHMALZ.COM/10.01.01.12784