


**Technical data**

Attribute	Value
Size	70.00
Temperature resistance	80.0 °C
Clamping range [mm]	65.0 ... 80.0 mm

SU 70

Suction cup cover SU is delivered in the desired diameter.

**Design data**

Attribute	Value
Outside diameter D2	30.0 mm
Outside diameter D	77.00 mm
Internal diameter d	5.00 mm

Design data SU 70

Art.-Nr.: 10.01.01.12838

**Technical data**

Attribute	Value
Weight	1.3 g
Size	70.00
Product family	SU
Clamping range [mm]	65.0 ... 80.0 mm

Note: In vertical applications with a suction plate or cup, the lateral force sinks by up to 70%. The vacuum generator must be able to provide 10% more suction power

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12838

