




Technical data

Attribute	Value
Size	40.00
Temperature resistance	80.0 °C
Clamping range [mm]	35.0 ... 45.0 mm

SU 40

Suction cup cover SU is delivered in the desired diameter.



Design data

Attribute	Value
Outside diameter D2	30.0 mm
Outside diameter D	47.00 mm
Internal diameter d	5.00 mm

Design data SU 40

Art.-Nr.: 10.01.01.12856

**Technical data**

Attribute	Value
Weight	0.5 g
Size	40.00
Product family	SU
Clamping range [mm]	35.0 ... 45.0 mm

Note: In vertical applications with a suction plate or cup, the lateral force sinks by up to 70%. The vacuum generator must be able to provide 10% more suction power

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12856

