

Flat suction cup (round)

SPF 60 ED-65 SC050



Art.-Nr.: 10.01.01.12896



Technical data


Suction cup material	Elastodur ED
Material hardness [Shore A]	65.0 Shore A
Size	60.00
Height H	18.10 mm

SPF 60 ED-65 SC050

Suction cup SPF (elastomer part + connection element) is delivered assembled. As an alternative the individual parts can also be ordered separately. To do this, the following ordering steps are required:

- Suction cup of type SPF (step 1) – elastomer part, available in various diameters
- Connection element of type SC (step 2) – available with various threads

Available accessories: filter screen



Design data

Height H2	7.50 mm
Height H	18.10 mm
Head diameter Dk	22.1 mm
Internal diameter d1	17.5 mm
Internal diameter d	10.50 mm
Spring stroke Z	5.1 mm
Diameter Ds	61.2 mm
Diameter Dmax(S)	65.0 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data SPF 60 ED-65 SC050



WWW.SCHMALZ.COM/10.01.01.12896

1

Art.-Nr.: 10.01.01.12896

**Technical data**

Nipple family	SC 050
Suction cup material	Elastodur ED
Material hardness [Shore A]	65.0 Shore A
Hose inner diameter (recom.) d	6.0 mm
Workpiece radius min. (convex)	70.0 mm
Pull-off force	135.00 N
Suction force (-600mbar)	107.00 N
Weight	9.00 g
Lateral force	65.0 N
Volume	12.669 cm ³
Size	60.00
Number of folds	0.0
Product family	SPF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Ordering Data Accessories 10.01.01.12896**

Typ		Item number
Schmalz-Connector	SC 050-AR NPT1/4-AG MOD	10.01.06.02543
Schmalz-Connector	SC 050-AR NPT1/4-IG MOD	10.01.06.02546
Sieve, round	SIEB 17.5x0.8 MS-A2 280 0.28/0.16	10.07.01.00308

