

Düz vantuz (yuvarlak)


## SGP 20 FPM-65 N016



Art.-Nr.: 10.01.01.12909



SGP 20 FPM-65 N016



Tasarım verileri SGP 20 FPM-65 N016

### Teknik veriler

Vantuz malzemesi	Fluorocautchuc FPM
Malzeme sertliği [Shore A]	65,0 Shore A
Boyut	20,00

### Tasarım verileri

Yükseklik H2	7,10 mm
Yükseklik H	10,40 mm
Kafa çapı Dk	11,0 mm
İç çap d	4,50 mm
Yay stroku Z	1,5 mm
Çap Ds	20,0 mm
Çap Dmax(S)	22,0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



[WWW.SCHMALZ.COM/10.01.01.12909](http://WWW.SCHMALZ.COM/10.01.01.12909)

Düz vantuz (yuvarlak)

## SGP 20 FPM-65 N016



Art.-Nr.: 10.01.01.12909



### Teknik veriler

Meme ucu ailesi	N 016
Vantuz malzemesi	Fluorocaotchuc FPM
Malzeme sertliđi [Shore A]	65,0 Shore A
Emme kuvveti (-600mbar)	8,50 N
Ađırlık	1,5 g
Cilt	0,599 cm <sup>3</sup>
Boyut	20,00
Körük Sayısı	0,0
Ürün ailesi	SGP

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



[WWW.SCHMALZ.COM/10.01.01.12909](http://WWW.SCHMALZ.COM/10.01.01.12909)