

Floating suction cup module
SBSm 14 90-3 4/2 0




Art.-Nr.: 10.01.01.12912



SBSm 14 90-3 4/2 0

Technical data

Attribute	Value
Connection	Hose 4/2
Length L	30.85 mm
Width B	14.00 mm
Slewing angle W	0.0 °
Angle of radiation	90.0 °
Number of holes	3



Design data SBSm 14 90-3 4/2 0

Design data

Attribute	Value
Length L	30.85 mm
Width B2	11.00 mm
Width B	14.00 mm
Height H	21.60 mm
Internal diameter d	4.20 mm
Slewing angle W	0.0 °
Angle of radiation	90.0 °
Thread G4	M4-M



Technical data

Attribute	Value
Weight	11.0 g
Pressure range (operating pressure) [bar]	0.5 ... 6.0 bar



WWW.SCHMALZ.COM/10.01.01.12912

Floating suction cup module
SBSm 14 90-3 4/2 0



Art.-Nr.: 10.01.01.12912



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12912



WWW.SCHMALZ.COM/10.01.01.12912