

Sealing ring for SGF suction plate

DR-SGF 150 HT1-60



Art.-Nr.: 10.01.01.13020




DR-SGF 150 HT1-60

Technical data

Attribute	Value
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Size	150.00
Height H	21.70 mm

Design data

Attribute	Value
Height H	21.70 mm
d2	125.0 mm
Spring stroke Z	3.3 mm
Diameter Ds	148.3 mm
Diameter Dmax(S)	156.0 mm



Design data DR-SGF 150 HT1-60



Art.-Nr.: 10.01.01.13020



Technical data

Attribute	Value
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Workpiece radius min. (convex)	2,000.0 mm
Suction force (-600mbar)	1,060.00 N
Weight	115.30 g
Volume	64.876 cm ³
Size	150.00
Number of folds	0.0
Product family	DR-SGF



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.13020

