



SPL 70 POM-NBR G1/4-IG

Vakum plakası SPL POM-NBR farklı çaplarda mevcuttur ve bağlanmaya hazır bir ürün olarak teslim edilir.


Teknik veriler

Attribute	Value
Vantuz malzemesi	Polioksimetilen perbunan POM-NBR
Boyut	70.00
Bağlantı	G1/4-IG

Tasarım verileri

Attribute	Value
Yükseklik H	24.50 mm
Kafa çapı Dk	73.0 mm
Dış G1	G1/4"-F
Dış uzunluğu LG1	11.5 mm
Anahtar boyutu SW1	22.0 mm
Yay stroku Z	3.0 mm
Çap Ds	68.0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



Tasarım verileri SPL 70 POM-NBR G1/4-IG

Art.-Nr.: 10.01.01.13107

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Polioksümetilen perbunan POM-NBR
Hortum çapı (tavsiye edilen) d	6.0 mm
Emme kuvveti (-600mbar)	217.00 N
Ağırlık	91.0 g
Cilt	24.100 cm ³
Bağlantı	G1/4-IG
Ürün ailesi	SPL

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.13107

**Yedek parçalar için sipariş verileri 10.01.01.13107**

Typ	Ürün numarası
V halkası	V-RING 63x13 V-65 S NBR
	10.07.08.00100

