



SPL 115 POM-NBR G1/4-IG

Vakum plakası SPL POM-NBR farklı çaplarda mevcuttur ve bağlanmaya hazır bir ürün olarak teslim edilir.


Teknik veriler

Attribute	Value
Vantuz malzemesi	Polioksimetilen perbunan POM-NBR
Boyut	115.00
Bağlantı	G1/4-IG

Tasarım verileri

Attribute	Value
Yükseklik H	30.50 mm
Kafa çapı Dk	118.0 mm
Diş G1	G1/4"-F
Diş uzunluğu LG1	12.0 mm
Anahtar boyutu SW1	22.0 mm
Yay stroku Z	4.0 mm
Çap Ds	113.0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



Tasarım verileri SPL 115 POM-NBR G1/4-IG

Art.-Nr.: 10.01.01.13110

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Polioksümetilen perbunan POM-NBR
Hortum çapı (tavsiye edilen) d	9.0 mm
Emme kuvveti (-600mbar)	600.00 N
Ağırlık	280.0 g
Cilt	91.200 cm ³
Bağlantı	G1/4-IG
Ürün ailesi	SPL

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.13110

**Yedek parçalar için sipariş verileri 10.01.01.13110**

Typ	Ürün numarası
V halkası	V-RING 105x18 V-110 S NBR
	10.07.08.00161

