




SPL-HT 120 FPM-F-65

Teknik veriler

Attribute	Value
Vantuz malzemesi	Fluorocaoutchuc FPM-F
Malzeme sertliği [Shore A]	65.0 Shore A
Boyut	120.00
Çalışma sıcaklığı maks.	350.0 °C



Tasarım verileri SPL-HT 120 FPM-F-65

Tasarım verileri

Attribute	Value
Yükseklik H2	5.00 mm
Yükseklik H	43.00 mm
Kafa çapı Dk	105.0 mm
İç çap d1	96.0 mm
d2	4.0 mm
İç çap d	88.00 mm
Yay stroku Z	25.0 mm
Çap Ds	120.0 mm
Yükseklik H3	10.00 mm
Çap Dmax(S)	130.0 mm

Art.-Nr.: 10.01.01.13435



Teknik veriler

Attribute	Value
Vantuz malzemesi	Fluorocautchuc FPM-F
İş parçası yarıçapı dak (dışbükey)	300.0 mm
Emme kuvveti (-600mbar)	675.00 N
Ağırlık	138.1 g
Cilt	255.000 cm ³
Boyut	120.00
Çalışma sıcaklığı maks.	350.0 °C
Ürün ailesi	SPL-HT

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.13435

