


DR-SGF-HS 150 EPDM-55



Art.-Nr.: 10.01.01.13491




DR-SGF-HS 150 EPDM-55

Technical data

Attribute	Value
Suction cup material	EPDM
Material hardness [Shore A]	55.0 Shore A
Size	150.00
Height H	25.90 mm

Design data

Attribute	Value
Height H	25.90 mm
d2	126.0 mm
Spring stroke Z	7.5 mm
Diameter Ds	148.5 mm
Diameter Dmax(S)	165.0 mm



Design data DR-SGF-HS 150 EPDM-55



Art.-Nr.: 10.01.01.13491



Technical data

Attribute	Value
Suction cup material	EPDM
Material hardness [Shore A]	55.0 Shore A
Workpiece radius min. (convex)	2,000.0 mm
Suction force (-600mbar)	1,060.00 N
Weight	111.2 g
Volume	119.000 cm ³
Size	150.00
Number of folds	0.0
Product family	DR-SGF



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.13491

