

Art.-Nr.: 10.01.01.13536




SUF 210 NBR-60 G1/2-IG VRS

Suction plate SUF (sealing ring + support plate) is delivered pre-assembled. The product consists of:

- Sealing ring of type DR-SUF – elastomer part, available in various diameters
- Reinforced plastic support plate with various threads

Available spare parts: sealing ring DR-SUF

Available accessories: touch valve TV, screen



Design data SUF 210 NBR-60 G1/2-IG VRS

Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60.0 Shore A
Size	210.00
contains	Screw plug
Suction cup area	380 cm ²

Design data

Attribute	Value
Length L2	46.50 mm
Height H	32.00 mm
d2	172.9 mm
Thread G1	G1/2"-F
Thread length LG1	12.2 mm
Thread G2	G1/4"-F
Thread length LG2	11.8 mm
Thread length LG3	11.1 mm
Dmk	100.0 mm
Spring stroke Z	11.0 mm



Art.-Nr.: 10.01.01.13536

**Technical data**

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60.0 Shore A
Hose inner diameter (recom.) d	12.0 mm
Workpiece radius min. (convex)	750.0 mm
Suction force (-600mbar)	2,070.00 N
Weight	546.0 g
Volume	362.000 cm ³
Size	210.00
Suction force d2	1,400.00 N
Product family	SUF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.13536

**Ordering Data Accessories 10.01.01.13536**

Typ		Item number
Sieve, round	SIEB 27x1 MS-A2 100 0.1/0.06	10.07.01.00110
Protection Covers	PC 250	10.01.01.13090
Touch Valve	TV G1/4-AG 12	10.05.10.00086

**Ordering Data Spare Parts 10.01.01.13536**

Typ		Item number
Sealing ring for SUF suction plate	DR-SUF 210 NBR-60	10.01.01.13846

