


Düz vantuz (yuvarlak)

SFF 15 SI-55 SC040



Art.-Nr.: 10.01.01.13746




SFF 15 SI-55 SC040

Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	15,00
Körük Sayısı	0,0

Tasarım verileri

Attribute	Value
Yükseklik H2	4,70 mm
Yükseklik H	12,50 mm
Kafa çapı Dk	13,0 mm
İç çap d1	10,4 mm
İç çap d	7,50 mm
Yay stroku Z	1,0 mm
Çap Ds	15,0 mm
Yükseklik H3	6,80 mm
Çap Dmax(S)	16,0 mm



Tasarım verileri SFF 15 SI-55 SC040



WWW.SCHMALZ.COM/10.01.01.13746

Art.-Nr.: 10.01.01.13746

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	SC 040
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55,0 Shore A
İş parçası yarıçapı dak (dışbükey)	12,5 mm
Çekme kuvveti	5,80 N
Emme kuvveti (-600mbar)	5,80 N
Ağırlık	0,90 g
Cilt	0,599 cm ³
Boyut	15,00
Körük Sayısı	0,0
Ürün ailesi	SFF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.13746

**Sipariş Verisi Aksesuarlar 10.01.01.13746**

Typ	Ürün numarası
Schmalz-Konnektör SC 040 M5-AG	10.01.06.04346
Schmalz-Konnektör SC 040 G1/8-AG	10.01.06.02490
Schmalz-Konnektör SC 040 G1/8-IG	10.01.06.02482

