

Düz vantuz (yuvarlak)

PFG 1.5 NBR-ESD-55 N002

Art.-Nr.: 10.01.01.13783




Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR-ESD
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	1,50

PFG 1.5 NBR-ESD-55 N002

Tasarım verileri



Attribute	Value
Yükseklik H	2,50 mm
Kafa çapı Dk	1,8 mm
İç çap d	1,20 mm
Yay stroku Z	0,1 mm
Çap Ds	1,5 mm
Çap Dmax(S)	1,8 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Tasarım verileri PFG 1.5 NBR-ESD-55 N002



WWW.SCHMALZ.COM/10.01.01.13783

Art.-Nr.: 10.01.01.13783

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	N 002
Vantuz malzemesi	Nitril kauçuk NBR-ESD
Malzeme sertliği [Shore A]	55,0 Shore A
İş parçası yarıçapı dak (dışbükey)	2,0 mm
Emme kuvveti (-600mbar)	0,06 N
Ağırlık	0,10 g
Cilt	0,003 cm ³
Boyut	1,50
Ürün ailesi	PFG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.13783

**Discontinued item**

The product family will be discontinued and is available until **31.12.2026**
Starting from this time, the article can no longer be ordered.
alternative article **10.01.01.14016 SUF 1.5 NBR-ESD-55 SC010**

**Sipariş Verisi Aksesuarlar 10.01.01.13783**

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N002 M3-AG DN70
	10.01.01.00314

WWW.SCHMALZ.COM/10.01.01.13783