


Düz vantuz (yuvarlak)

PFG 10 NBR-ESD-55 N004

Art.-Nr.: 10.01.01.13785



PFG 10 NBR-ESD-55 N004



Tasarım verileri PFG 10 NBR-ESD-55 N004

Teknik veriler

Vantuz malzemesi	Nitril kauçuk NBR-ESD
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	10,00

Tasarım verileri

Yükseklik H2	2,00 mm
Yükseklik H	7,50 mm
Kafa çapı Dk	8,7 mm
İç çap d1	6,0 mm
İç çap d	4,00 mm
Yay stroku Z	1,4 mm
Çap Ds	10,0 mm
Yükseklik H3	4,00 mm
Çap Dmax(S)	11,5 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



WWW.SCHMALZ.COM/10.01.01.13785

Düz vantuz (yuvarlak)

PFG 10 NBR-ESD-55 N004



Art.-Nr.: 10.01.01.13785



Teknik veriler

Meme ucu ailesi	N 004
Vantuz malzemesi	Nitril kauçuk NBR-ESD
Malzeme sertliđi [Shore A]	55,0 Shore A
İş parçası yarıçapı dak (dışbükey)	12,5 mm
Cilt	0,154 cm ³
Boyut	10,00
Ürün ailesi	PFG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Sipariş Verisi Aksesuarlar 10.01.01.13785

Typ		Ürün numarası
Vantuz bağlantı nipeli	SA-NIP N004 M5-AG DN200	10.01.01.03526
Vantuz bağlantı nipeli	SA-NIP N004 M5-IG DN200	10.01.01.03518



WWW.SCHMALZ.COM/10.01.01.13785