


Düz vantuz (yuvarlak)

PFG 5 NBR-ESD-55 N004


Art.-Nr.: 10.01.01.13787



Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR-ESD
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	5,00

PFG 5 NBR-ESD-55 N004



Tasarım verileri

Attribute	Value
Yükseklik H2	2,00 mm
Yükseklik H	6,50 mm
Kafa çapı Dk	7,7 mm
İç çap d1	6,0 mm
İç çap d	4,00 mm
Yay stroku Z	0,9 mm
Çap Ds	5,0 mm
Yükseklik H3	4,00 mm
Çap Dmax(S)	5,5 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Tasarım verileri PFG 5 NBR-ESD-55 N004



WWW.SCHMALZ.COM/10.01.01.13787

Art.-Nr.: 10.01.01.13787

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	N 004
Vantuz malzemesi	Nitril kauçuk NBR-ESD
Malzeme sertliği [Shore A]	55,0 Shore A
İş parçası yarıçapı dak (dışbükey)	7,5 mm
Emme kuvveti (-600mbar)	0,75 N
Cilt	0,092 cm ³
Boyut	5,00
Ürün ailesi	PFG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.13787

**Sipariş Verisi Aksesuarlar 10.01.01.13787**

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N004 M5-AG DN200 10.01.01.03526
Vantuz bağlantı nipel	SA-NIP N004 M5-IG DN200 10.01.01.03518

WWW.SCHMALZ.COM/10.01.01.13787