


Flat suction cup (round)

SUF 5 NBR-55 SC020


Art.-Nr.: 10.01.01.13940



SUF 5 NBR-55 SC020

Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55.0 Shore A
Size	5.00



Design data SUF 5 NBR-55 SC020

Design data

Attribute	Value
Height H2	2.30 mm
Height H	5.50 mm
Head diameter Dk	6.7 mm
Internal diameter d1	4.7 mm
Internal diameter d	3.10 mm
Spring stroke Z	0.5 mm
Diameter Ds	5.0 mm
Height H3	3.00 mm
Diameter Dmax(S)	5.7 mm



WWW.SCHMALZ.COM/10.01.01.13940

Art.-Nr.: 10.01.01.13940

**Technical data**

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55.0 Shore A
Workpiece radius min. (convex)	8.0 mm
Pull-off force	0.90 N
Suction force (-600mbar)	0.90 N
Weight	0.1 g
Volume	0.013 cm ³
Size	5.00
Product family	SUF
Interface nipple family	SC020

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.13940

**Ordering Data Accessories 10.01.01.13940**

Typ		Item number
Schmalz-Connector	SC 020 M5-AG	10.01.06.04273
Schmalz-Connector	SC 020 M5-IG	10.01.06.04306

