


Flat suction cup (round)

SUF 40 NBR-55 SC050



Art.-Nr.: 10.01.01.13951



SUF 40 NBR-55 SC050

Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55.0 Shore A
Size	40.00



Design data SUF 40 NBR-55 SC050

Design data

Attribute	Value
Height H2	6.80 mm
Height H	16.00 mm
Head diameter Dk	24.8 mm
Internal diameter d1	17.2 mm
Internal diameter d	11.00 mm
Spring stroke Z	4.0 mm
Diameter Ds	40.0 mm
Height H3	9.30 mm
Diameter Dmax(S)	44.0 mm



WWW.SCHMALZ.COM/10.01.01.13951

Art.-Nr.: 10.01.01.13951

**Technical data**

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55.0 Shore A
Workpiece radius min. (convex)	50.0 mm
Pull-off force	61.00 N
Suction force (-600mbar)	61.00 N
Weight	8.50 g
Volume	3.800 cm ³
Size	40.00
Product family	SUF
Interface nipple family	SC050

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.13951

**Ordering Data Accessories 10.01.01.13951**

Typ		Item number
Schmalz-Connector	SC 050 G1/8-AG	10.01.06.04250
Schmalz-Connector	SC 050 G1/8-IG	10.01.06.04308

