

Плоская присоска (круглая)

SUF 60 NBR-55 M10x1.25-IG N009



Art.-Nr.: 10.01.01.13953



Технические данные

Attribute	Value
Материал присоски	Нитрильный каучук NBR
Твердость материала [Shore A]	55,0 Shore A
размер	60,00

SUF 60 NBR-55 M10x1.25-IG N009

Присоска SUF (эластомер+соединительный ниппель) поставляется собранной.

Доступные запасные части: присоска SUF, соединительный ниппель SC

Конструктивные данные

Attribute	Value
Высота H	17,00 mm
Резьба G1	M10x1.25-F
Длина резьбы LG1	6,0 mm
Ход пружины Z	5,5 mm
Диаметр Ds	60,0 mm
Диаметр Dmax(S)	66,4 mm

Конструктивные данные SUF 60 NBR-55 M10x1.25-IG N009



WWW.SCHMALZ.COM/10.01.01.13953

Art.-Nr.: 10.01.01.13953



Технические данные

Attribute	Value
Материал присоски	Нитрильный каучук NBR
Твердость материала [Shore A]	55,0 Shore A
Внутренний диаметр шланга (реком.) d	6,0 mm
Радиус заготовки мин. (выпуклый)	75,0 mm
Сила отрыва	140,00 N
Всасывающая сила (-600 мбар)	140,00 N
Вес	31,0 g
Объем	12,700 cm ³
размер	60,00
Семейство продуктов	SUF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.13953



Данные для заказа Аксессуары 10.01.01.13953

Тип	Количество предметов
Сенсорный клапан TVN G1/4-AG 9 N009	10.05.10.00065

