

Düz vantuz (yuvarlak)

SUF 70 NBR-55 M10x1.25-IG N009



Art.-Nr.: 10.01.01.13954



Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
Boyut	70.00

SUF 70 NBR-55 M10x1.25-IG N009

Vantuz SUF (elastomer parça + konektör) monte edilmiş olarak teslim edilir.

Mevcut yedek parçalar: vantuz SUF, konektör SC

Tasarım verileri

Attribute	Value
Yükseklik H	17.50 mm
Diş G1	M10x1.25-F
Diş uzunluğu LG1	6.0 mm
Yay stroku Z	6.0 mm
Çap Ds	70.0 mm
Çap Dmax(S)	77.2 mm

Tasarım verileri SUF 70 NBR-55 M10x1.25-IG N009



WWW.SCHMALZ.COM/10.01.01.13954

Düz vantuz (yuvarlak)

SUF 70 NBR-55 M10x1.25-IG N009



Art.-Nr.: 10.01.01.13954



Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
Hortum çapı (tavsiye edilen) d	6.0 mm
İş parçası yarıçapı dak (dışbükey)	100.0 mm
Çekme kuvveti	198.00 N
Emme kuvveti (-600mbar)	198.00 N
Ağırlık	52.0 g
Cilt	18.000 cm ³
Boyut	70.00
Ürün ailesi	SUF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.13954



Veri aksesuarları sipariş edin 10.01.01.13954

Typ	Ürün numarası
Temas Valfi	TVN G1/4-AG 9 N009
	10.05.10.00065



WWW.SCHMALZ.COM/10.01.01.13954