

Flat suction cup (round)

SUF 15 SI-55 SC030


Art.-Nr.: 10.01.01.13967



SUF 15 SI-55 SC030

Technical data

Attribute	Value
Suction cup material	Silicone SI
Material hardness [Shore A]	55.0 Shore A
Size	15.00
Material characteristics	FDA-compatible



Design data

Attribute	Value
Height H2	4.30 mm
Height H	8.90 mm
Head diameter Dk	9.8 mm
Internal diameter d1	7.3 mm
Internal diameter d	5.30 mm
Spring stroke Z	1.5 mm
Diameter Ds	15.0 mm
Height H3	5.80 mm
Diameter Dmax(S)	16.8 mm

Design data SUF 15 SI-55 SC030



WWW.SCHMALZ.COM/10.01.01.13967

Flat suction cup (round)

SUF 15 SI-55 SC030



Art.-Nr.: 10.01.01.13967



Technical data

Attribute	Value
Suction cup material	Silicone SI
Material hardness [Shore A]	55.0 Shore A
Workpiece radius min. (convex)	20.0 mm
Pull-off force	9.00 N
Suction force (-600mbar)	9.00 N
Weight	0.73 g
Volume	0.220 cm ³
Size	15.00
Product family	SUF
Interface nipple family	SC030

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.13967



Ordering Data Accessories 10.01.01.13967

Typ		Item number
Schmalz-Connector	SC 030 G1/8-AG	10.01.06.04288
Schmalz-Connector	SC 030 G1/8-IG	10.01.06.04307



WWW.SCHMALZ.COM/10.01.01.13967