

Flat suction cup (round)

SUF 25 SI-55 SC040



Art.-Nr.: 10.01.01.13970



SUF 25 SI-55 SC040

Technical data

Attribute	Value
Suction cup material	Silicone SI
Material hardness [Shore A]	55.0 Shore A
Size	25.00
Material characteristics	FDA-compatible



Design data

Attribute	Value
Height H2	4.80 mm
Height H	11.20 mm
Head diameter Dk	15.5 mm
Internal diameter d1	10.5 mm
Internal diameter d	7.00 mm
Spring stroke Z	2.5 mm
Diameter Ds	25.0 mm
Height H3	6.70 mm
Diameter Dmax(S)	28.2 mm

Design data SUF 25 SI-55 SC040



WWW.SCHMALZ.COM/10.01.01.13970

Flat suction cup (round)

SUF 25 SI-55 SC040



Art.-Nr.: 10.01.01.13970



Technical data

Attribute	Value
Suction cup material	Silicone SI
Material hardness [Shore A]	55.0 Shore A
Workpiece radius min. (convex)	25.0 mm
Pull-off force	23.00 N
Suction force (-600mbar)	23.00 N
Weight	2.50 g
Volume	0.900 cm ³
Size	25.00
Product family	SUF
Interface nipple family	SC040

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.13970



Ordering Data Accessories 10.01.01.13970

Typ		Item number
Schmalz-Connector	SC 040 G1/8-AG	10.01.06.02490
Schmalz-Connector	SC 040 G1/8-IG	10.01.06.02482



WWW.SCHMALZ.COM/10.01.01.13970