

Flat suction cup (round)

SUF 70 SI-55 M10x1.25-IG N009



Art.-Nr.: 10.01.01.13976



SUF 70 SI-55 M10x1.25-IG N009

Suction cup SUF (elastomer part + connector) is delivered assembled.

Available spare parts: suction cup SUF, connector SC

Technical data

Attribute	Value
Suction cup material	Silicone SI
Material hardness [Shore A]	55.0 Shore A
Size	70.00
Material characteristics	FDA-compatible

Design data

Attribute	Value
Height H	17.50 mm
Thread G1	M10x1.25-F
Thread length LG1	6.0 mm
Spring stroke Z	6.0 mm
Diameter Ds	70.0 mm
Diameter Dmax(S)	77.2 mm

Design data SUF 70 SI-55 M10x1.25-IG N009



WWW.SCHMALZ.COM/10.01.01.13976

Art.-Nr.: 10.01.01.13976

**Technical data**

Attribute	Value
Suction cup material	Silicone SI
Material hardness [Shore A]	55.0 Shore A
Hose inner diameter (recom.) d	6.0 mm
Workpiece radius min. (convex)	100.0 mm
Pull-off force	198.00 N
Suction force (-600mbar)	198.00 N
Weight	52.0 g
Volume	18.000 cm ³
Size	70.00
Product family	SUF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.13976

**Ordering Data Accessories 10.01.01.13976**

Typ	Item number
Touch Valve	TVN G1/4-AG 9 N009
	10.05.10.00065

