

Flat suction cup (round)

SUF 5 HT1-60 SC020




Art.-Nr.: 10.01.01.13984



Technical data

Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Size	5.00

SUF 5 HT1-60 SC020



Design data

Height H2	2.30 mm
Height H	5.50 mm
Head diameter Dk	6.7 mm
Internal diameter d1	4.7 mm
Internal diameter d	3.10 mm
Spring stroke Z	0.5 mm
Diameter Ds	5.0 mm
Height H3	3.00 mm
Diameter Dmax(S)	5.7 mm

Design data SUF 5 HT1-60 SC020



WWW.SCHMALZ.COM/10.01.01.13984

1

Flat suction cup (round)

SUF 5 HT1-60 SC020



Art.-Nr.: 10.01.01.13984



Technical data

Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Workpiece radius min. (convex)	8.0 mm
Pull-off force	0.90 N
Suction force (-600mbar)	0.90 N
Weight	0.14 g
Volume	0.013 cm ³
Size	5.00
Product family	SUF
Interface nipple family	SC020

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Ordering Data Accessories 10.01.01.13984

Typ		Item number
Schmalz-Connector	SC 020 M5-AG	10.01.06.04273
Schmalz-Connector	SC 020 M5-IG	10.01.06.04306



WWW.SCHMALZ.COM/10.01.01.13984