


Flat suction cup (round)

SUF 10 HT1-60 SC030


Art.-Nr.: 10.01.01.13987



SUF 10 HT1-60 SC030

Technical data

Attribute	Value
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Size	10.00



Design data

Attribute	Value
Height H2	4.30 mm
Height H	8.40 mm
Head diameter Dk	9.5 mm
Internal diameter d1	7.3 mm
Internal diameter d	5.30 mm
Spring stroke Z	1.0 mm
Diameter Ds	10.0 mm
Height H3	5.80 mm
Diameter Dmax(S)	11.2 mm

Design data SUF 10 HT1-60 SC030



WWW.SCHMALZ.COM/10.01.01.13987

Art.-Nr.: 10.01.01.13987

**Technical data**

Attribute	Value
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Workpiece radius min. (convex)	12.5 mm
Pull-off force	4.00 N
Suction force (-600mbar)	4.00 N
Weight	0.5 g
Volume	0.070 cm ³
Size	10.00
Product family	SUF
Interface nipple family	SC030

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.13987

**Ordering Data Accessories 10.01.01.13987**

Typ		Item number
Schmalz-Connector	SC 030 G1/8-AG	10.01.06.04288
Schmalz-Connector	SC 030 G1/8-IG	10.01.06.04307

