


Flat suction cup (round)

SUF 18 HT1-60 SC030

Art.-Nr.: 10.01.01.13990



SUF 18 HT1-60 SC030

Technical data

Attribute	Value
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Size	18.00



Design data

Attribute	Value
Height H2	4.30 mm
Height H	9.30 mm
Head diameter Dk	11.5 mm
Internal diameter d1	7.3 mm
Internal diameter d	5.30 mm
Spring stroke Z	1.8 mm
Diameter Ds	18.0 mm
Height H3	5.80 mm
Diameter Dmax(S)	20.6 mm

Design data SUF 18 HT1-60 SC030



WWW.SCHMALZ.COM/10.01.01.13990

Flat suction cup (round)

SUF 18 HT1-60 SC030



Art.-Nr.: 10.01.01.13990



Technical data

Attribute	Value
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Workpiece radius min. (convex)	20.0 mm
Pull-off force	13.00 N
Suction force (-600mbar)	13.00 N
Weight	1.1 g
Volume	0.370 cm ³
Size	18.00
Product family	SUF
Interface nipple family	SC030

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.13990



Ordering Data Accessories 10.01.01.13990

Typ		Item number
Schmalz-Connector	SC 030 G1/8-AG	10.01.06.04288
Schmalz-Connector	SC 030 G1/8-IG	10.01.06.04307



WWW.SCHMALZ.COM/10.01.01.13990