

Düz vantuz (yuvarlak)

SUF 100 HT1-60 M10x1.25-IG N009



Art.-Nr.: 10.01.01.14001



SUF 100 HT1-60 M10x1.25-IG N009

Vantuz SUF (elastomer parça + konektör) monte edilmiş olarak teslim edilir.

Mevcut yedek parçalar: vantuz SUF, konektör SC

Teknik veriler

Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60,0 Shore A
Boyut	100,00

Tasarım verileri

Yükseklik H	19,00 mm
Diş G1	M10x1.25-F
Diş uzunluğu LG1	6,0 mm
Yay stroku Z	7,5 mm
Çap Ds	100,0 mm
Çap Dmax(S)	108,0 mm

Tasarım verileri SUF 100 HT1-60 M10x1.25-IG N009



WWW.SCHMALZ.COM/10.01.01.14001

Düz vantuz (yuvarlak)

SUF 100 HT1-60 M10x1.25-IG N009



Art.-Nr.: 10.01.01.14001



Teknik veriler

Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60,0 Shore A
Hortum çapı (tavsiye edilen) d	6,0 mm
İş parçası yarıçapı dak (dışbükey)	200,0 mm
Çekme kuvveti	402,00 N
Emme kuvveti (-600mbar)	402,00 N
Ağırlık	104,50 g
Cilt	46,400 cm ³
Boyut	100,00
Ürün ailesi	SUF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Sipariş Verisi Aksesuarlar 10.01.01.14001

Typ	Ürün numarası
Temas Valfi	TVN G1/4-AG 9 N009
	10.05.10.00065



WWW.SCHMALZ.COM/10.01.01.14001