

Flat suction cup (round)

SUF 100 HT1-60 M10x1.25-IG N009



Art.-Nr.: 10.01.01.14001



Technical data

Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Size	100.00

SUF 100 HT1-60 M10x1.25-IG N009

Suction cup SUF (elastomer part + connector) is delivered assembled.

Available spare parts: suction cup SUF, connector SC

Design data

Height H	19.00 mm
Thread G1	M10x1.25-F
Thread length LG1	6.0 mm
Spring stroke Z	7.5 mm
Diameter Ds	100.0 mm
Diameter Dmax(S)	108.0 mm

Design data SUF 100 HT1-60 M10x1.25-IG N009



WWW.SCHMALZ.COM/10.01.01.14001

Flat suction cup (round)

SUF 100 HT1-60 M10x1.25-IG N009



Art.-Nr.: 10.01.01.14001



Technical data

Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Hose inner diameter (recom.) d	6.0 mm
Workpiece radius min. (convex)	200.0 mm
Pull-off force	402.00 N
Suction force (-600mbar)	402.00 N
Weight	104.50 g
Volume	46.400 cm ³
Size	100.00
Product family	SUF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Ordering Data Accessories 10.01.01.14001

Typ		Item number
Touch Valve	TVN G1/4-AG 9 N009	10.05.10.00065



WWW.SCHMALZ.COM/10.01.01.14001