

Flat suction cup (round)

SUF 1 SI-CO-55 SC010


Art.-Nr.: 10.01.01.14015



SUF 1 SI-CO-55 SC010

Technical data

Attribute	Value
Suction cup material	Silicone SI conductive
Material hardness [Shore A]	55.0 Shore A
Size	1.00



Design data SUF 1 SI-CO-55 SC010

Design data

Attribute	Value
Height H2	2.00 mm
Height H	2.60 mm
Head diameter Dk	2.5 mm
Internal diameter d	1.50 mm
Spring stroke Z	0.1 mm
Diameter Ds	1.0 mm
Diameter Dmax(S)	1.1 mm



WWW.SCHMALZ.COM/10.01.01.14015

Art.-Nr.: 10.01.01.14015

**Technical data**

Attribute	Value
Suction cup material	Silicone SI conductive
Material hardness [Shore A]	55.0 Shore A
Workpiece radius min. (convex)	2.0 mm
Pull-off force	0.03 N
Suction force (-600mbar)	0.03 N
Weight	0.0 g
Volume	0.000 cm ³
Size	1.00
Product family	SUF
Interface nipple family	SC010

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.14015

**Ordering Data Accessories 10.01.01.14015**

Typ	Item number
Schmalz-Connector	SC 010 M3-AG
	10.01.06.04249

