

Flat suction cup (round)

SUF 4 NBR-ESD-55 SC010




Art.-Nr.: 10.01.01.14020



Technical data

Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55.0 Shore A
Size	4.00

SUF 4 NBR-ESD-55 SC010



Design data

Height H2	2.00 mm
Height H	3.50 mm
Head diameter Dk	4.2 mm
Internal diameter d	1.40 mm
Spring stroke Z	0.4 mm
Diameter Ds	4.0 mm
Diameter Dmax(S)	4.7 mm

Design data SUF 4 NBR-ESD-55 SC010



WWW.SCHMALZ.COM/10.01.01.14020

Flat suction cup (round)

SUF 4 NBR-ESD-55 SC010



Art.-Nr.: 10.01.01.14020



Technical data

Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55.0 Shore A
Workpiece radius min. (convex)	8.0 mm
Pull-off force	0.40 N
Suction force (-600mbar)	0.40 N
Weight	0.04 g
Volume	0.005 cm ³
Size	4.00
Product family	SUF
Interface nipple family	SC010

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Ordering Data Accessories 10.01.01.14020

Typ	Item number
Schmalz-Connector SC 010 M3-AG	10.01.06.04249



WWW.SCHMALZ.COM/10.01.01.14020