

Düz vantuz (yuvarlak)

SFF 10 EPDM-45 SC030



Art.-Nr.: 10.01.01.14044




SFF 10 EPDM-45 SC030

Teknik veriler

Attribute	Value
Vantuz malzemesi	EPDM
Malzeme sertliği [Shore A]	45,0 Shore A
Boyut	10,00
Körük Sayısı	0,0

Tasarım verileri

Attribute	Value
Yükseklik H2	4,20 mm
Yükseklik H	10,40 mm
Kafa çapı Dk	9,3 mm
İç çap d1	7,3 mm
İç çap d	5,50 mm
Yay stroku Z	0,7 mm
Çap Ds	10,0 mm
Yükseklik H3	5,90 mm
Çap Dmax(S)	11,0 mm



Tasarım verileri SFF 10 EPDM-45 SC030



WWW.SCHMALZ.COM/10.01.01.14044

Art.-Nr.: 10.01.01.14044

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	SC 030
Vantuz malzemesi	EPDM
Malzeme sertliği [Shore A]	45,0 Shore A
İş parçası yarıçapı dak (dışbükey)	8,0 mm
Çekme kuvveti	3,00 N
Emme kuvveti (-600mbar)	2,70 N
Ağırlık	0,40 g
Cilt	0,245 cm ³
Boyut	10,00
Körük Sayısı	0,0
Ürün ailesi	SFF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.14044

**Sipariş Verisi Aksesuarlar 10.01.01.14044**

Typ	Ürün numarası
Schmalz-Konnektör	SC 030 M5-AG
	10.01.06.02802

