


Flat suction cup (round)

SFF 25 HT1-60 SC040



Art.-Nr.: 10.01.01.14053




SFF 25 HT1-60 SC040

Technical data

Attribute	Value
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Size	25.00
Number of folds	0.0

Design data

Attribute	Value
Height H2	4.70 mm
Height H	13.20 mm
Head diameter Dk	13.8 mm
Internal diameter d1	10.4 mm
Internal diameter d	7.50 mm
Spring stroke Z	1.7 mm
Diameter Ds	25.0 mm
Height H3	6.80 mm
Diameter Dmax(S)	26.5 mm



Design data SFF 25 HT1-60 SC040



WWW.SCHMALZ.COM/10.01.01.14053

Art.-Nr.: 10.01.01.14053

**Technical data**

Attribute	Value
Nipple family	SC 040
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Workpiece radius min. (convex)	25.0 mm
Pull-off force	17.90 N
Suction force (-600mbar)	17.90 N
Weight	1.8 g
Volume	1.154 cm ³
Size	25.00
Number of folds	0.0
Product family	SFF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.14053

**Ordering Data Accessories 10.01.01.14053**

Typ		Item number
Schmalz-Connector	SC 040 G1/8-AG	10.01.06.02490
Schmalz-Connector	SC 040 G1/8-IG	10.01.06.02482

**Ordering Data Spare Parts 10.01.01.14053**

Typ		Item number
Schmalz-Connector	SC 040 M5-AG	10.01.06.04346

