


Düz vantuz (yuvarlak)

SFF 40 HT1-60 SC050



Art.-Nr.: 10.01.01.14055




SFF 40 HT1-60 SC050

Teknik veriler

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60.0 Shore A
Boyut	40.00
Körük Sayısı	0.0

Tasarım verileri

Attribute	Value
Yükseklik H2	6.60 mm
Yükseklik H	19.00 mm
Kafa çapı Dk	21.9 mm
İç çap d1	17.1 mm
İç çap d	11.40 mm
Yay stroku Z	2.7 mm
Çap Ds	40.0 mm
Yükseklik H3	9.50 mm
Çap Dmax(S)	42.0 mm



Tasarım verileri SFF 40 HT1-60 SC050



WWW.SCHMALZ.COM/10.01.01.14055

Art.-Nr.: 10.01.01.14055

**Teknik veriler**

Attribute	Value
Meme ucu ailesi	SC 050
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60.0 Shore A
İş parçası yarıçapı dak (dışbükey)	45.0 mm
Çekme kuvveti	47.40 N
Emme kuvveti (-600mbar)	47.40 N
Ağırlık	6.7 g
Cilt	4.331 cm ³
Boyut	40.00
Körük Sayısı	0.0
Ürün ailesi	SFF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.14055

**Veri aksesuarları sipariş edin 10.01.01.14055**

Typ	Ürün numarası
Schmalz-Konnektör	SC 050 G1/4-AG SW410
Schmalz-Konnektör	SC 050 G1/4-IG SW410

