

Düz vantuz (yuvarlak)

SUF 80 NBR-55 G1/4-AG



Art.-Nr.: 10.01.01.14059



SUF 80 NBR-55 G1/4-AG


Vantuz SUF (elastomer parça + konektör) monte edilmiş olarak teslim edilir.

Mevcut yedek parçalar: vantuz SUF, konektör SC

Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	80,00
Vakum bağlantısı	G1/4"-M

Tasarım verileri



Attribute	Value
Yükseklik H	23,00 mm
Nominal çap dn	5,10 mm
Diş G1	G1/4"-M
Diş uzunluğu LG1	10,0 mm
Anahtar boyutu SW1	17,0 mm
Yay stroku Z	6,5 mm
Çap Ds	80,0 mm
Çap Dmax(S)	87,1 mm

Tasarım verileri SUF 80 NBR-55 G1/4-AG



WWW.SCHMALZ.COM/10.01.01.14059

Art.-Nr.: 10.01.01.14059

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55,0 Shore A
Hortum çapı (tavsiye edilen) d	6,0 mm
İş parçası yarıçapı dak (dışbükey)	100,0 mm
Çekme kuvveti	254,00 N
Emme kuvveti (-600mbar)	254,00 N
Ağırlık	71,10 g
Cilt	25,100 cm ³
Boyut	80,00
Körük Sayısı	0,0
Ürün ailesi	SUF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.14059

WWW.SCHMALZ.COM/10.01.01.14059