


Düz vantuz (yuvarlak)

SUF 100 HT1-60 G1/4-IG



Art.-Nr.: 10.01.01.14087




Teknik veriler

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60,0 Shore A
Boyut	100,00
Vakum bağlantısı	G1/4"-F

SUF 100 HT1-60 G1/4-IG

Vantuz SUF (elastomer parça + konektör) monte edilmiş olarak teslim edilir.

Mevcut yedek parçalar: vantuz SUF, konektör SC



Tasarım verileri

Attribute	Value
Yükseklik H	35,90 mm
Nominal çap dn	5,10 mm
Diş G1	G1/4"-F
Diş uzunluğu LG1	12,0 mm
Anahtar boyutu SW1	17,0 mm
Yay stroku Z	7,5 mm
Çap Ds	100,0 mm
Çap Dmax(S)	108,0 mm

Tasarım verileri SUF 100 HT1-60 G1/4-IG



WWW.SCHMALZ.COM/10.01.01.14087

Art.-Nr.: 10.01.01.14087



Teknik veriler

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60,0 Shore A
Hortum çapı (tavsiye edilen) d	6,0 mm
İş parçası yarıçapı dak (dışbükey)	200,0 mm
Çekme kuvveti	402,00 N
Emme kuvveti (-600mbar)	402,00 N
Ağırlık	113,80 g
Cilt	46,400 cm ³
Boyut	100,00
Körük Sayısı	0,0
Ürün ailesi	SUF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.14087



WWW.SCHMALZ.COM/10.01.01.14087