

Düz vantuz (yuvarlak)

SUF 50 NBR-55 G1/8-AG



Art.-Nr.: 10.01.01.14091




Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	50,00
Vakum bağlantısı	G1/8"-M

SUF 50 NBR-55 G1/8-AG

Vantuz SUF (elastomer parça + konektör) monte edilmiş olarak teslim edilir.

Mevcut yedek parçalar: vantuz SUF, konektör SC



Tasarım verileri

Attribute	Value
Yükseklik H	24,20 mm
Nominal çap dn	4,10 mm
Diş G1	G1/8"-M
Diş uzunluğu LG1	7,5 mm
Anahtar boyutu SW1	17,0 mm
Yay stroku Z	5,0 mm
Çap Ds	50,0 mm
Çap Dmax(S)	54,3 mm

Tasarım verileri SUF 50 NBR-55 G1/8-AG



WWW.SCHMALZ.COM/10.01.01.14091

Art.-Nr.: 10.01.01.14091

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55,0 Shore A
Hortum çapı (tavsiye edilen) d	4,0 mm
İş parçası yarıçapı dak (dışbükey)	75,0 mm
Çekme kuvveti	95,00 N
Emme kuvveti (-600mbar)	95,00 N
Ağırlık	23,10 g
Cilt	7,100 cm ³
Boyut	50,00
Körük Sayısı	0,0
Ürün ailesi	SUF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.14091

**Sipariş Verisi Yedek Parça 10.01.01.14091**

Typ	Ürün numarası
Schmalz-Konnektör	SC 050 G1/8-AG
Düz vantuz (yuvarlak)	SUF 50 NBR-55 SC050

