


Düz vantuz (yuvarlak)

SUF 40 NBR-55 G1/8-IG



Art.-Nr.: 10.01.01.14094




Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	40,00
Vakum bağlantısı	G1/8"-F

SUF 40 NBR-55 G1/8-IG

Vantuz SUF (elastomer parça + konektör) monte edilmiş olarak teslim edilir.

Mevcut yedek parçalar: vantuz SUF, konektör SC



Tasarım verileri

Attribute	Value
Yükseklik H	30,00 mm
Nominal çap dn	6,10 mm
Dış G1	G1/8"-F
Dış uzunluğu LG1	8,0 mm
Anahtar boyutu SW1	17,0 mm
Yay stroku Z	4,0 mm
Çap Ds	40,0 mm
Çap Dmax(S)	44,0 mm

Tasarım verileri SUF 40 NBR-55 G1/8-IG



WWW.SCHMALZ.COM/10.01.01.14094

Art.-Nr.: 10.01.01.14094

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55,0 Shore A
Hortum çapı (tavsiye edilen) d	4,0 mm
İş parçası yarıçapı dak (dışbükey)	50,0 mm
Çekme kuvveti	61,00 N
Emme kuvveti (-600mbar)	61,00 N
Ağırlık	18,90 g
Cilt	3,800 cm ³
Boyut	40,00
Körük Sayısı	0,0
Ürün ailesi	SUF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.14094

**Sipariş Verisi Yedek Parça 10.01.01.14094**

Typ	Ürün numarası
Schmalz-Konnektör	SC 050 G1/8-IG
Düz vantuz (yuvarlak)	SUF 40 NBR-55 SC050

