


Flat suction cup (round)

SUF 15 NBR-ESD-55 G1/8-AG

Art.-Nr.: 10.01.01.14121



SUF 15 NBR-ESD-55 G1/8-AG

Suction cup SUF (elastomer part + connector) is delivered assembled.


Available spare parts: suction cup SUF, connector SC

Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55.0 Shore A
Size	15.00
Vacuum connection	G1/8"-M

Design data

Attribute	Value
Height H	15.00 mm
Nominal diameter dn	3.10 mm
Thread G1	G1/8"-M
Thread length LG1	7.5 mm
Key width SW1	14.0 mm
Spring stroke Z	1.5 mm
Diameter Ds	15.0 mm
Diameter Dmax(S)	16.8 mm



Design data SUF 15 NBR-ESD-55 G1/8-AG



WWW.SCHMALZ.COM/10.01.01.14121

Art.-Nr.: 10.01.01.14121

**Technical data**

Attribute	Value
Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	20.0 mm
Pull-off force	9.00 N
Suction force (-600mbar)	9.00 N
Weight	4.7 g
Volume	0.220 cm ³
Size	15.00
Number of folds	0.0
Product family	SUF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.14121

**Ordering Data Spare Parts 10.01.01.14121**

Typ		Item number
Schmalz-Connector	SC 030 G1/8-AG	10.01.06.04288
Flat suction cup (round)	SUF 15 NBR-ESD-55 SC030	10.01.01.14032

