

Flat suction cup (round)

SUF 20 SI-55 G1/8-AG



Art.-Nr.: 10.01.01.14131




Technical data

Suction cup material	Silicone SI
Material hardness [Shore A]	55.0 Shore A
Size	20.00
Vacuum connection	G1/8"-M
Material characteristics	FDA-compatible

SUF 20 SI-55 G1/8-AG

Suction cup SUF (elastomer part + connector) is delivered assembled.

Available spare parts: suction cup SUF, connector SC



Design data

Height H	15.50 mm
Nominal diameter dn	3.10 mm
Thread G1	G1/8"-M
Thread length LG1	7.5 mm
Key width SW1	14.0 mm
Spring stroke Z	2.0 mm
Diameter Ds	20.0 mm
Diameter Dmax(S)	22.8 mm

Design data SUF 20 SI-55 G1/8-AG



WWW.SCHMALZ.COM/10.01.01.14131

1

Flat suction cup (round)

SUF 20 SI-55 G1/8-AG



Art.-Nr.: 10.01.01.14131



Technical data

Suction cup material	Silicone SI
Material hardness [Shore A]	55.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	20.0 mm
Pull-off force	15.00 N
Suction force (-600mbar)	15.00 N
Weight	5.50 g
Volume	0.500 cm ³
Size	20.00
Number of folds	0.0
Product family	SUF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Ordering Data Spare Parts 10.01.01.14131

Typ		Item number
Schmalz-Connector	SC 030 G1/8-AG	10.01.06.04288
Flat suction cup (round)	SUF 20 SI-55 SC030	10.01.01.13969



WWW.SCHMALZ.COM/10.01.01.14131